

SIX YEAR WARRANTY



MADE IN THE USA

Go Getter

Portable Sound System



Perfect for...

- Indoor & Outdoor Events
- Parks & Recreation
- Fitness Centers
- Schools
- Group Classes
- House of Worship
- Corporate Events
- Auctions
- Rental
- and more!



FEATURES

- Reaches crowds of 500+
- 109 dB of clear sound
- 75W AC mode / 50W DC mode
- Up to two built-in wireless receivers
- Standard built-in Bluetooth
- Optional CD/MP3 combo player
- Two universal microphone jack inputs
- 3.5 mm AUX line input
- Built-in rechargeable battery operates 6 - 8 hours on a single charge
- One high-output horn tweeter
- One 6.5" woven fiber woofer
- External speaker output powers optional Go Getter unpowered companion speaker



(GG-8000CU2 Back Panel)

Go Getter Models

GG-8000	Go Getter with Bluetooth
GG-8000U1	Go Getter with Bluetooth & 1 wireless receiver
GG-8000U2	Go Getter with Bluetooth & 2 wireless receivers
GG-8000C	Go Getter with Bluetooth & CD/MP3 combo player
GG-8000CU1	Go Getter with Bluetooth, CD/MP3 combo player & 1 wireless receiver
GG-8000CU2	Go Getter with Bluetooth, CD/MP3 combo player & 2 wireless receivers
GG-8001	Go Getter unpowered companion speaker
Wireless Microphones & Transmitters	
WH-8000	Wireless handheld microphone
WB-8000	Wireless beltpack transmitter (requires handsfree microphone) Microphone options include: Headband/HBM-TA4F, Collar/CM-60, Over-the-Ear/EM-TA4F, or Lapel/LM-60

Technical Specifications

Rated Power Output	75 watts AC / 50 watts DC
Max SPL @ Rated Power	109 dB @ 1 meter
Battery	One 12V sealed lead acid rechargeable, 9.0 AH Full recharge: approx 7 hrs
Wireless Range	150' line of sight
Line Output (post fader)	isolated, 600 W, 1/4" phone
DC Power	19 VDC, 60 watts max
Dimensions (HWD)	18" X 10" X 11.5" (45.7 X 25.4 X 29.2 cm)
Weight	18.5 lbs / 8.4 Kg
Mic Inputs:	Lo-Z (1 KW), balanced, XLR 12 VDC condenser mic (phantom) power Hi-Z (10 KW), unbalanced, 1/4" phone
Line In	1/4" balanced, 3.5 mm stereo
Outputs	
Speaker Out	4-pole Neutrik Speakon® jack

(Features & Specifications Subject to Change Without Notice)



AIR MODEL FEATURES



GG-8000XU2

- One built-in AIR wireless companion transmitter
- One built-in AIR wireless receiver
- Expandable to multiple AIR battery powered wireless companion speakers
- Easily connects to Assistive Listening
- ADA Compliant
- Built-in rechargeable batteries operate 6 - 8 hours on a single charge
- Alternate wired and wireless mode
- External speaker output powers optional Go Getter unpowered or AIR companion speaker

**All other features are the same as the Go Getter 8000 series except option of CD/MP3 combo player*



GG-AIR

GG-AIR Technical Specifications

AIR Frequency Range	902.000 - 928.000 MHz
Wireless Range	150' line of sight
Weight	19 lbs / 8.6 Kg
Speaker In	4-pole Neutrik Speakon® input

**All other features are the same as the Liberty Platinum 8000 series*

Go Getter AIR Models

GG-8000X	Go Getter with AIR wireless companion transmitter
GG-8000XU1	Go Getter with 1 wireless receiver & AIR wireless companion transmitter
GG-8000XU2	Go Getter with 2 wireless receivers & AIR wireless companion transmitter
GG-AIR	Go Getter AIR battery powered wireless companion speaker

Go Getter AIR Packages

GG-DP-AIR	<ul style="list-style-type: none"> - GG-8000XU1 with Bluetooth, AIR wireless companion transmitter, and one wireless receiver - Go Getter AIR battery powered wireless companion speaker (GG-AIR) - Two heavy duty speaker stands (SS-550) - Choice of one wireless transmitter: <ul style="list-style-type: none"> - Wireless handheld mic (WH-8000) or - Beltpack transmitter (WB-8000) with choice of one mic: <ul style="list-style-type: none"> - Headband mic (HBM-TA4F) - Collar mic (CM-60) - UltraLite mic (EM-TA4F) - Lapel mic (LM-60) - Includes 3.5 mm AUX cable
GG-DPDUAL-AIR	<ul style="list-style-type: none"> - GG-8000XU2 with Bluetooth, AIR wireless companion transmitter, and two wireless receivers - Go Getter AIR battery powered wireless companion speaker (GG-AIR) - Two heavy duty speaker stands (SS-550) - Choice of two wireless transmitters: <ul style="list-style-type: none"> - Wireless handheld mic (WH-8000) or - Beltpack transmitter (WB-8000) with choice of one mic: <ul style="list-style-type: none"> - Headband mic (HBM-TA4F) - Collar mic (CM-60) - UltraLite mic (EM-TA4F) - Lapel mic (LM-60) - Includes 3.5 mm AUX cable

(Features & Specifications Subject to Change Without Notice)



800.262.4671

www.anchoraudio.com

Anchor AIR System Arrangement



FREQUENTLY ASKED QUESTIONS

Q: How does the AIR wireless connection work?

A: Simple! An 8000X, 8000XU1, and 8000XU2 (Liberty, Go Getter, & MegaVox) include a built-in transmitter - as designated by the X. This transmitter operates on the 902 – 928 MHz frequency with 100 user-selectable channels. The AIR wireless companion speakers have a built-in receiver which, when set to the same channel as the transmitter, picks up the audio signal.

Q: Can I use multiple AIR companion speakers in one set up?

A: Yes, absolutely. Any 8000X, 8000XU1, or 8000XU2 can transmit to an unlimited number of AIR wireless companion speakers. All units should be set to the same frequency to receive signal. When setting up your arrangement, be sure to point the systems facing the same direction – pointing the systems directly at one another may cause distortion. AIR units can be placed 150 feet (or more in ideal conditions) from the transmitting main unit.

Q: The battery in my AIR is dead/I am experiencing interference on all channels. Can I connect with a cable instead of the wireless connection?

A: Yes! All AIR units have what we call 'Wired Mode' which allows the AIR wireless companion speaker to be used just like an unpowered wired companion speaker. Power and audio signal are sent from the main unit to the AIR companion speaker with a cable. Simply power off the companion speaker, flip the switch into 'Wired Mode,' plug in your speaker cable (SC-50NL for Liberty & Go Getter, SC-50 for MegaVox), and the main unit will power the companion.

Q: What is the range of the AIR wireless companion speaker?

A: Each AIR can be placed up to 150 feet from the main unit transmitter. In ideal conditions, you can place the systems further, however, be aware of physical latency and/or interference. If you are using multiple AIR systems, be sure to center the main unit between all AIR companions.

Q: I am experiencing interference with my AIR wireless companion, what can I do?

A: Oh no! You have a few options. First, try to change the channel. There are 100 channels to choose from, so be sure to try various frequencies to find a clear channel. You should also double check that your speakers are close enough together to have a strong signal. Be sure all your batteries are fully charged. Additionally, verify your inputs all have a clear signal (such as a wireless microphone, cables, and Bluetooth). Lastly, you can try adjusting the external antennas for a better connection. These fixes may not work for everyone, as there are occasional signals which cannot be avoided (for example being close to a high-power cell tower). In this situation, you can use your AIR companion in 'Wired Mode'. If none of these fixes work, please call us. We are happy to help!

Q: Since the Anchor Audio Assistive Listening Devices are also on 902 – 928 MHz, can they work together to create a simple and reliable ADA compliant sound system?

A: Actually, yes! An 8000X, 8000XU1, and 8000XU2 (Liberty, Go Getter, & MegaVox) will transmit to the AIR companion speakers as well as the Assistive Listening ALB-9000 belt-pack(s). Since all systems are shipped out by default on the 902.000 channel, simply power on your transmitter and receivers (belt-packs and AIR wireless companion), and you instantly have an ADA compliant sound system. Did you know that ADA requirements mandate compliant assistive listening systems for any theater using audio amplification or with a capacity of at least 50 audience members? Try this set up for the easiest solution.